



75163591

IP20

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	No
----------------------------------	----

Function	for switch, push-button, dimmer and shutter functions
----------	-------------------------------------------------------

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--------------------------------------------

Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	3
-------------------	---

Operation	activation of second user level via object ; one push-button operation for switching, pushing, shutters and dimming
-----------	---------------------------------------------------------------------------------------------------------------------

Dimensions

Height	88.5 mm
--------	---------

Width	88.5 mm
-------	---------

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	-----------------------------------------------------------------------------------------

Screen

With display	No
--------------	----

Materials

Colour of design line	glass polar white
-----------------------	-------------------

Colour	polarwhite
--------	------------

Type of surface treatment	Painted
---------------------------	---------

LED control

LED	with blue operation LED and 6 white status LEDs (labelling field illumination)
-----	--------------------------------------------------------------------------------

Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

Settings

Supported configuration modes	system, PB
-------------------------------	------------

Parameterisation	single and two push-button operation parameterisable
------------------	------------------------------------------------------

Subject to technical modifications

Scope of delivery

Bus connection included	No
-------------------------	----

Accessories included

Box	for installation in single standard wall boxes
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x ; for glass frames in the same "style" for additional applications, see the Design line B.7

Equipment

Number of actuation points	6
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

Safety

Protection index IP	IP20
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX ; Berker B.IQ