




75163774



Technical properties

Architecture

| | |
|-------------|----------------|
| Fixing mode | flush-mounting |
|-------------|----------------|

Functions

| | |
|----------------------------------|----|
| With room temperature controller | No |
|----------------------------------|----|

| | |
|----------|---|
| Function | for switch, push-button, dimmer and shutter functions |
|----------|---|

Compatibility

| | |
|----------------|--|
| Extension unit | extension unit for light scene push-button |
|----------------|--|

Controls and indicators

| | |
|---------------------|-----|
| With LED indication | Yes |
|---------------------|-----|

| | |
|-------------------|---|
| Number of buttons | 3 |
|-------------------|---|

| | |
|-----------|--|
| Operation | one push-button operation for switching, pushing, shutters and dimming, activation of second user level via object |
|-----------|--|

Dimensions

| | |
|--------------------------------|----------------|
| Labelling field length (W x H) | 66.8 x 15.7 mm |
|--------------------------------|----------------|

| | |
|--------|---------|
| Height | 52.8 mm |
|--------|---------|

| | |
|-------|---------|
| Width | 66.8 mm |
|-------|---------|

Measurement

| | |
|-------------------|---|
| Value transmitter | value transmitter for dimming, position, brightness and temperature values 1 and 2 byte |
|-------------------|---|

Screen

| | |
|--------------|----|
| With display | No |
|--------------|----|

Materials

| | |
|--------|-----------|
| Colour | aluminium |
|--------|-----------|

| | |
|------------|----------------------------|
| RAL colour | RAL 9006 - White aluminium |
|------------|----------------------------|

| | |
|----------|---------------|
| Material | thermoplastic |
|----------|---------------|

| | |
|-----------------------|-------|
| Material for printing | Paper |
|-----------------------|-------|

| | |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

| | |
|-----------------|---------|
| Material family | Plastic |
|-----------------|---------|

LED control

| | |
|-----|--|
| LED | with white operation LED and 6 red status LEDs |
|-----|--|

Connection

| | |
|-------------------|-------------------------------------|
| Bus coupling unit | for bus coupling unit flush-mounted |
|-------------------|-------------------------------------|

| | |
|--|---|
| Settings | |
| Parameterisation | single and two push-button operation parameterisable |
| Scope of delivery | |
| Bus connection included | No |
| Equipment | |
| Number of actuation points | 6 |
| With anti-theft/dismantling protection | Yes |
| Type of configuration | Beschriftungsfeld(er) - Folie |
| Product type: | product type: push-button 3gang |
| Use | |
| Differentiation characteristic 1 - Sales | with labelling fields |
| Differentiation characteristic 3 - Sales | with horizontal operation |
| Safety | |
| Protection index IP | IP20 |
| Protection | with dismantling protection |
| Alarm | alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte |
| Use conditions | |
| Operating temperature | -5...45 °C |
| Storage/transport temperature | -20...70 °C (storage at > 45°C reduces the service life) |
| Identification | |
| Application, usage | KNX - operating systems |
| Product family | product family: push-button |
| Main design line | KNX - Berker K.1 |
| Secondary design line(s) | KNX, Berker K.1 |