




75164685



Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 4

Operation one push-button operation for switching, pushing, shutters and dimming, lockable via 3-button actuation, second operating level via object or 3-button handle

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of design line anthracite

Colour anthracite

RAL colour RAL 7021 - Black grey

Material thermoplastic

Surface appearance matt

Type of surface treatment untreated

Material family Plastic

LED control

LED with green operation LED and 8 red status LEDs

Connection

Bus coupling unit for bus coupling unit flush-mounted

Settings

Parameterisation single and two push-button operation parameterisable

Scope of delivery	
Bus connection included	No
Equipment	
Number of actuation points	8
With anti-theft/dismantling protection	Yes
Product type:	product type: push-button 4gang
Use	
Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	with vertical operation
Safety	
Protection index IP	IP20
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX, Berker S.1, Berker B.3, Berker B.7