



75164770



Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	No
----------------------------------	----

Function	for switch, push-button, dimmer and shutter functions
----------	---

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	4
-------------------	---

Operation	second operating level via object or 3-button handle, one push-button operation for switching, pushing, shutters and dimming, lockable via 3-button actuation
-----------	---

Dimensions

Labelling field length (W x H)	66.8 x 25 mm
--------------------------------	--------------

Height	111.1 mm
--------	----------

Width	70.5 mm
-------	---------

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of design line	polar white
-----------------------	-------------

Colour	polarwhite
--------	------------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	thermoplastic
----------	---------------

Material for printing	Paper
-----------------------	-------

Type of surface treatment	untreated
---------------------------	-----------

Material family	Plastic
-----------------	---------

LED control

LED	with white operation LED and 8 red status LEDs
-----	--

Connection

Settings

Parameterisation	single and two push-button operation parameterisable
------------------	--

Scope of delivery

Bus connection included	No
-------------------------	----

Equipment

Number of actuation points	8
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 4gang

Use

Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with horizontal operation

Safety

Protection index IP	IP20
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	Berker K.1, KNX

Instructions

Special note text	Use only in combination with frame frame with large cut-out.
-------------------	--