



75261271

**KNX cont. 2.2 m, KNX - K.5, al., matt, lacq.**

#### Technical properties

##### Functions

Function	parameter defineable lock function
----------	------------------------------------

##### Compatibility

Extension unit	also suitable as extension unit
----------------	---------------------------------

##### Controls and indicators

Number of switching segments	72
------------------------------	----

##### Dimensions

Dimensions assembling height	23.5 mm
Nominal mounting height	2.2 m

##### Measurement

Detection field, semi-oval shaped	≈ 12 x 12 m
-----------------------------------	-------------

##### Reach distance

Range, frontal	≈ 12 m
Range, frontal (at 1.1 m installation height)	≈ 6 m
Range, side	each ≈ 6 m
Range, side (at 1.1 m installation height)	each ≈ 3 m

##### Cover, door

Cover	with cover to limit detection angle to 90°
-------	--

##### Detection

Number of detection levels	2
Detection angle	180 °
Sensor type	detector of movement

##### Materials

RAL colour	RAL 9006 - White aluminium
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

##### Lighting control

Response brightness, configurable	1...1000 lx / daytime operation
-----------------------------------	---------------------------------

##### Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

<b>Settings</b>	
Supported configuration modes	system
Response sensitivity, settable	20...100 %
Delay time	≈ 10 s
Additional delay time programmable	130 ms...152 h
Setting	with potentiometer for fine adjustment of the response sensitivity
<b>Equipment</b>	
Product type:	product type: movement
<b>Use conditions</b>	
Operating temperature	-5...45 °C
<b>Identification</b>	
Application, usage	KNX - sensors
Product family	product family: physical sensors
Main design line	KNX - Berker K.5
Secondary design line(s)	KNX, Berker K.5, Motion detector
<b>Instructions</b>	
Information text	Application as for order no. 7526 11 ..