



75261289



**KNX cont. 2.2 m, KNX - S.1/B.3/B.7, p. white, matt, plastic**

#### Technical properties

##### Functions

Function	parameter defineable lock function
----------	------------------------------------

##### Compatibility

Extension unit	also suitable as extension unit
----------------	---------------------------------

##### Controls and indicators

Number of switching segments	72
------------------------------	----

##### Dimensions

Dimensions assembling height	23.5 mm
------------------------------	---------

Nominal mounting height	2.2 m
-------------------------	-------

##### Measurement

Detection field, semi-oval shaped	≈ 12 x 12 m
-----------------------------------	-------------

##### Reach distance

Range, frontal	≈ 12 m
----------------	--------

Range, frontal (at 1.1 m installation height)	≈ 6 m
---	-------

Range, side	each ≈ 6 m
-------------	------------

Range, side (at 1.1 m installation height)	each ≈ 3 m
--	------------

##### Cover, door

Cover	with cover to limit detection angle to 90°
-------	--

##### Detection

Number of detection levels	2
----------------------------	---

Detection angle	180 °
-----------------	-------

Sensor type	detector of movement
-------------	----------------------

##### Materials

Colour of design line	polar white
-----------------------	-------------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Surface appearance	matt
--------------------	------

##### Lighting control

Response brightness, configurable	1...1000 lx / daytime operation
-----------------------------------	---------------------------------

##### Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

##### Settings

Supported configuration modes	system
Response sensitivity, settable	20...100 %
Delay time	≈ 10 s
Additional delay time programmable	130 ms...152 h
Setting	with potentiometer for fine adjustment of the response sensitivity

**Equipment**

Product type:	product type: movement
---------------	------------------------

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

**Identification**

Application, usage	KNX - sensors
Product family	product family: physical sensors
Main design line	KNX - Berker S.1/B.3/B.7
Secondary design line(s)	Motion detector ; Berker B.3 ; Berker S.1 ; Berker B.7 ; KNX

**Instructions**

Information text	Application as for order no. 7526 11 ..
------------------	---