



47527204

**SCHUKO soc.out. hinged cover, enhanced contact prot., K.5, steel, matt finish**

**Technical properties**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

**Cover, door**

Hinged covers with self-closing hinged covers

Cover Central cover plate

**Materials**

Colour of design line Stainless steel

Material / workmanship metal, matt finish

Surface appearance matt

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 1 - Sales Labelling field

Differentiation characteristic 2 - Sales enhanced contact protection

**Safety**

IK protection code against mechanical impacts 07

|                                  |                             |
|----------------------------------|-----------------------------|
| Protection index IP              | IP44                        |
| Halogen free                     | No                          |
| Protection                       | Enhanced contact protection |
| With enhanced contact protection | Yes                         |

**Identification**

|                    |                                     |
|--------------------|-------------------------------------|
| Application, usage | Flush-mounted wet-room installation |
| Main design line   | Berker K.5                          |

**Instructions**

|                   |  |
|-------------------|--|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200).                 |
| Information text  | Labelling field height arranged for 6 mm P-touch strips. Specially suited to combinations of several socket outlets if right angle plugs are used. |