



5031

Rocker push-button NO contact Module insert

Technical properties

Architecture

Type of control unit	rocker
----------------------	--------

Functions

Switching angle	3.5 °
-----------------	-------

Configuration

Switch mode	Normally open contact
-------------	-----------------------

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

Electric current

Momentary-contact current	10 A
---------------------------	------

Dimensions

Depth	41.6 mm
Insertion depth	30 mm
Contact spacing	> 3 mm
Height	70.8 mm
Width	70.8 mm

Materials

Material	Plastic/metal
----------	---------------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Conductor cross-section (rigid)	2.5
Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with plug-in terminals

Scope of delivery

With lamp	No
-----------	----

Equipment

Quantity of NC contacts	0
-------------------------	---

Quantity of NO contacts	1
-------------------------	---

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

Use cases

Application	Barrier-free application, HVAC-control, Light control
-------------	---

Safety

Protection index IP	IP20
---------------------	------

Identification

Application, usage	Light control
--------------------	---------------

Main design line	Light control
------------------	---------------

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--