



503501

Series push-button NC contact and NO contacts with isolated input terminals

Technical properties

Architecture

Type of control unit double rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode 1 NO, 1 NC, separate input terminals

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Insertion depth 31.3 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

Equipment

Lighting can be illuminated using neon lamp, incandescent or LED unit with N terminal ; for lighting and monitoring circuit

Use cases

Application Light control

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Identification

Application, usage	Light control
Main design line	Light control

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--
