


75141226



IP20



Technical properties

Functions

| | |
|----------------------------------|---|
| With room temperature controller | No |
| Function | for switch, push-button, dimmer and shutter functions |

Compatibility

| | |
|----------------|--|
| Extension unit | extension unit for light scene push-button |
|----------------|--|

Controls and indicators

| | |
|---------------------|-----|
| With LED indication | Yes |
| Number of buttons | 1 |

Dimensions

| | |
|--------------------------------|---------|
| Labelling field length (W x H) | 56.4 mm |
| Height | 71 mm |
| Width | 71 mm |

Measurement

| | |
|-------------------|---|
| Value transmitter | dimming / position value transmitter 1 byte |
|-------------------|---|

Screen

| | |
|--------------|----|
| With display | No |
|--------------|----|

Materials

| | |
|-----------------------|-------------|
| Colour of labelling | 217,217,217 |
| Colour of design line | anthracite |
| Material for printing | Paper |
| Surface appearance | velvety |
| Material family | Plastic |

LED control

| | |
|-----|--|
| LED | with white operation LED and 2 amber status LEDs |
|-----|--|

Scope of delivery

| | |
|-------------------------|-----|
| Bus connection included | Yes |
|-------------------------|-----|

Equipment

| | |
|--|---------------------------------|
| Number of actuation points | 2 |
| With anti-theft/dismantling protection | Yes |
| Type of configuration | Beschriftungsfeld(er) - Folie |
| Product type: | product type: push-button 1gang |

Use

| | |
|--|----------------------|
| Differentiation characteristic 1 - Sales | with labelling field |
|--|----------------------|

| | |
|--|---------------------------------|
| Differentiation characteristic 3 - Sales | with integral bus coupling unit |
|--|---------------------------------|

Safety

| | |
|------------|-----------------------------|
| Protection | with dismantling protection |
|------------|-----------------------------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...45 °C |
|-----------------------|------------|

Identification

| | |
|--------------------|-------------------------|
| Application, usage | KNX - operating systems |
|--------------------|-------------------------|

| | |
|----------------|-----------------------------|
| Product family | product family: push-button |
|----------------|-----------------------------|

| | |
|------------------|----------------------|
| Main design line | KNX - Berker Q.1/Q.3 |
|------------------|----------------------|

| | |
|--------------------------|-------------------------------|
| Secondary design line(s) | Berker Q.1 ; Berker Q.3 ; KNX |
|--------------------------|-------------------------------|

Instructions

| | |
|------------------|--|
| Information text | Labelling field sheet, order no. 9498 29 01, available separately. |
|------------------|--|