



75143326

IP20



Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Light scenes retrieval, adjustment and storage of 8 light scenes

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 3

Operation one push-button operation for switching, pushing, shutters and dimming

Dimensions

Labelling field length (W x H) 56.4 x 17 mm

Height 71 mm

Width 71 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of labelling 217,217,217

Colour of design line anthracite

Colour anthracite

RAL colour RAL 7021 - Black grey

Material Plastic/metal

Material for printing Paper

Surface appearance velvety

Type of surface treatment Painted

Material family Plastic

LED control

LED

with white operation LED and 6 amber status LEDs

Settings

Supported configuration modes system

Parameterisation single and two push-button operation parameterisable

Scope of delivery

Bus connection included Yes

Equipment

Number of actuation points 6

With anti-theft/dismantling protection Yes

Type of configuration Beschriftungsfeld(er) - Folie

Product type: product type: push-button 3gang

Controller extension unit usable as thermostat extension unit

Use

Differentiation characteristic 1 - Sales with labelling fields

Differentiation characteristic 3 - Sales with integral bus coupling unit

Safety

Protection index IP IP20

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C

Identification

Application, usage KNX - operating systems

Product family product family: push-button

Main design line KNX - Berker Q.1/Q.3

Secondary design line(s) Berker Q.3, Berker Q.7, Berker Q.1

Instructions

Information text Labelling field sheet, order no. 9498 31 03, available separately.