



75161093



**IP20**

**B.IQ push-button 1gang, KNX - B.IQ, stainless steel, metal brushed**

**Technical properties**

**Functions**

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

**Compatibility**

Extension unit extension unit for light scene push-button

**Controls and indicators**

With LED indication Yes

Number of buttons 1

**Dimensions**

Assembling height 16.7 mm

Height 88.5 mm

Width 88.5 mm

**Measurement**

Value transmitter dimming / position value transmitter 1 byte

**Screen**

With display No

**Materials**

Colour of design line Stainless steel

Material / workmanship metal brushed

Surface appearance matt

**LED control**

LED with blue operation LED and 2 white status LEDs (labelling field illumination)

**Connection**

Bus coupling unit for bus coupling unit flush-mounted

**Scope of delivery**

Bus connection included No

**Accessories included**

Box for installation in single standard wall boxes

for stainless steel frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Matching products

---

**Equipment**

---

Number of actuation points	2
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

---

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

---

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

**Identification**

---

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	Berker B.IQ ; KNX