




75161373

IP20



Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 1

Dimensions

Labelling field length (W x H) 66.8 x 52.8 mm

Height 52.8 mm

Width 66.8 mm

Measurement

Value transmitter dimming / position value transmitter 1 byte

Screen

With display No

Materials

Colour of design line stainless steel

Colour stainless steel

RAL colour RAL 9022 - Pearl light grey

Material Plastic/metal

Material for printing Paper

Surface appearance matt

Type of surface treatment Painted

Material family Plastic

LED control

LED - KNX with white operation LED and 2 red status LEDs

Connection

Bus coupling unit for bus coupling unit flush-mounted

Scope of delivery

Bus connection included	No
-------------------------	----

Equipment

Number of actuation points	2
----------------------------	---

With anti-theft/dismantling protection	Yes
--	-----

Type of configuration	Beschriftungsfeld(er) - Folie
-----------------------	-------------------------------

Product type:	product type: push-button 1gang
---------------	---------------------------------

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Differentiation characteristic 3 - Sales	with horizontal operation
--	---------------------------

Safety

Protection index IP	IP20
---------------------	------

Protection	with dismantling protection
------------	-----------------------------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
--------------------	-------------------------

Product family	product family: push-button
----------------	-----------------------------

Secondary design line(s)	Berker K.5, Radio bus, KNX
--------------------------	----------------------------