



75663592



## B.IQ push-button 3gang thermostat, display, KNX - B.IQ, glass black

### Technical properties

#### Functions

With room temperature controller	Yes
Function	with valve protection function
Timers	with room temperature timer and 2-week timer functions

#### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

#### Controls and indicators

With LED indication	Yes
Number of buttons	3
Operation	one push-button operation for switching, pushing, shutters and dimming

#### Dimensions

Width of rail mounted device (RMD)	0 modules
Height	119.6 mm
Width	88.5 mm

#### Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

#### Materials

Colour of design line	glass black
RAL colour	RAL 9005 - Jet black
Material	glass
Material family	Glass

#### LED control

LED	with blue operation LED and 6 white status LEDs (labelling field illumination)
-----	--

#### Settings

Parameterisation	single and two push-button operation parameterisable
------------------	--

#### Accessories included

Box	for installation in single standard wall boxes
Matching products	for glass frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

**Equipment**

---

Product type:	product type: B.IQ
Control	for individual single room temperature control

---

**Software**

---

Update	with flash-controller technology
--------	----------------------------------

---

**Safety**

---

Protection	with dismantling protection
------------	-----------------------------

---

**Use conditions**

---

Operating temperature	-5...45 °C
Energy efficiency class	IV (2%)

---

**Identification**

---

Application, usage	KNX - operating systems
Product family	product family: push-button
Release issue	2.6
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ

---