





75162683



IP20



Technical properties

Functions

With room temperature controller	No
----------------------------------	----

Function	for switch, push-button, dimmer and shutter functions
----------	---

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	2
-------------------	---

Operation	one push-button operation for switching, pushing, shutters and dimming ; activation of second user level via object
-----------	---

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of design line	aluminium
-----------------------	-----------

Material / workmanship	lacquered
------------------------	-----------

Surface appearance	matt
--------------------	------

Material family	Plastic
-----------------	---------

LED control

LED	with green operation LED and 4 red status LEDs
-----	--

Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

Settings

Parameterisation	single and two push-button operation parameterisable
------------------	--

Scope of delivery

Bus connection included	No
-------------------------	----

Equipment

Number of actuation points	4
----------------------------	---

With anti-theft/dismantling protection	Yes
--	-----

Product type:	product type: push-button 2gang
Use	
Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	with vertical operation
Safety	
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX ; Berker S.1 ; Berker B.3 ; Berker B.7