



75163774



IP20



Technical properties

Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Number of buttons	3
Operation	one push-button operation for switching, pushing, shutters and dimming ; activation of second user level via object

Dimensions

Labelling field length (W x H)	66.8 x 15.7 mm
Height	52.8 mm
Width	66.8 mm

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of labelling	105,105,105
Colour of design line	aluminium
Material for printing	Paper
Surface appearance	glossy
Type of surface treatment	untreated
Material family	Plastic

LED control

LED	with white operation LED and 6 red status LEDs
-----	--

Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

Settings

Parameterisation	single and two push-button operation parameterisable
------------------	--

Scope of delivery

Bus connection included	No
-------------------------	----

Equipment

Number of actuation points	6
----------------------------	---

With anti-theft/dismantling protection	Yes
--	-----

Type of configuration	Beschriftungsfeld(er) - Folie
-----------------------	-------------------------------

Product type:	product type: push-button 3gang
---------------	---------------------------------

Use

Differentiation characteristic 1 - Sales	with labelling fields
--	-----------------------

Differentiation characteristic 3 - Sales	with horizontal operation
--	---------------------------

Safety

Protection	with dismantling protection
------------	-----------------------------

Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
-------	---

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

Identification

Application, usage	KNX - operating systems
--------------------	-------------------------

Product family	product family: push-button
----------------	-----------------------------

Main design line	KNX - Berker K.1
------------------	------------------

Secondary design line(s)	KNX ; Berker K.1
--------------------------	------------------