


75163775



## Technical properties

### Architecture

Fixing mode flush-mounting

### Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

### Compatibility

Extension unit extension unit for light scene push-button

### Controls and indicators

With LED indication Yes

Number of buttons 3

Operation one push-button operation for switching, pushing, shutters and dimming, activation of second user level via object

### Dimensions

Labelling field length (W x H) 66.8 x 15.7 mm

Height 52.8 mm

Width 66.8 mm

### Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

### Screen

With display No

### Materials

Colour of labelling 217,217,217

Colour of design line anthracite

Colour anthracite

RAL colour RAL 7021 - Black grey

Material thermoplastic

Material for printing Paper

Type of surface treatment untreated

Material family Plastic

### LED control

LED with white operation LED and 6 red status LEDs

**Connection**

Bus coupling unit for bus coupling unit flush-mounted

**Settings**

Parameterisation single and two push-button operation parameterisable

**Scope of delivery**

Bus connection included No

**Equipment**

Number of actuation points 6

With anti-theft/dismantling protection Yes

Type of configuration Beschriftungsfeld(er) - Folie

Product type: product type: push-button 3gang

**Use**

Differentiation characteristic 1 - Sales with labelling fields

Differentiation characteristic 3 - Sales with horizontal operation

**Safety**

Protection index IP IP20

Protection with dismantling protection

Alarm alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

**Use conditions**

Operating temperature -5...45 °C

Storage/transport temperature -20...70 °C (storage at > 45°C reduces the service life)

**Identification**

Application, usage KNX - operating systems

Product family product family: push-button

Secondary design line(s) Berker K.1, KNX