



75164591

### Technical properties

#### Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

#### Compatibility

Extension unit extension unit for light scene push-button

#### Controls and indicators

With LED indication Yes

Number of buttons 4

Operation second operating level via object or 3-button handle ; lockable via 3-button actuation ; one push-button operation for switching, pushing, shutters and dimming

#### Dimensions

Height 118.1 mm

Width 88.5 mm

#### Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

#### Screen

With display No

#### Materials

Colour of design line glass polar white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

#### LED control

LED with blue operation LED and 8 white status LEDs (labelling field illumination)

#### Connection

Bus coupling unit for bus coupling unit flush-mounted

#### Settings

Supported configuration modes system, PB

Parameterisation single and two push-button operation parameterisable

#### Scope of delivery

Bus connection included

No

### Accessories included

Box for installation in single standard wall boxes

Matching products

for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x ; for glass frames in the same "style" for additional applications, see the Design line B.7

### Equipment

Number of actuation points 8

With anti-theft/dismantling protection Yes

Product type: product type: B.IQ

### Safety

Protection with dismantling protection

Alarm alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

### Use conditions

Operating temperature -5...45 °C

### Identification

Application, usage KNX - operating systems

Product family product family: push-button

Main design line KNX - Berker B.IQ

Secondary design line(s) KNX ; Berker B.IQ