



75164774



Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 4

Operation second operating level via object or 3-button handle, one push-button operation for switching, pushing, shutters and dimming, lockable via 3-button actuation

Dimensions

Labelling field length (W x H) 66.8 x 25 mm

Height 111.1 mm

Width 70.5 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour aluminium

RAL colour RAL 9006 - White aluminium

Material thermoplastic

Material for printing Paper

Type of surface treatment untreated

Material family Plastic

LED control

LED with white operation LED and 8 red status LEDs

Connection

Bus coupling unit for bus coupling unit flush-mounted

Settings	
Parameterisation	single and two push-button operation parameterisable
Scope of delivery	
Bus connection included	No
Accessories included	
Box	for installation in single standard wall boxes
Equipment	
Number of actuation points	8
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 4gang
Use cases	
Frame	only for frame with large cut-out
Use	
Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with horizontal operation
Safety	
Protection index IP	IP20
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
Use conditions	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX, Berker K.1