




75164785



Berker S.1/B.3/B.7 Push Button 4-gang, Comfort with Label, Anthracite/Aluminium

Technical properties

Functions

| | |
|----------------------------------|----|
| With room temperature controller | No |
|----------------------------------|----|

| | |
|----------|---|
| Function | for switch, push-button, dimmer and shutter functions |
|----------|---|

Compatibility

| | |
|----------------|--|
| Extension unit | extension unit for light scene push-button |
|----------------|--|

Controls and indicators

| | |
|---------------------|-----|
| With LED indication | Yes |
|---------------------|-----|

| | |
|-------------------|---|
| Number of buttons | 4 |
|-------------------|---|

| | |
|-----------|---|
| Operation | one push-button operation for switching, pushing, shutters and dimming ; lockable via 3-button actuation ; second operating level via object or 3-button handle |
|-----------|---|

Dimensions

| | |
|--------------------------------|----------------|
| Labelling field length (W x H) | 52.3 x 24.9 mm |
|--------------------------------|----------------|

| | |
|--------|----------|
| Height | 110.7 mm |
|--------|----------|

| | |
|-------|-------|
| Width | 56 mm |
|-------|-------|

Measurement

| | |
|-------------------|---|
| Value transmitter | value transmitter for dimming, position, brightness and temperature values 1 and 2 byte |
|-------------------|---|

Screen

| | |
|--------------|----|
| With display | No |
|--------------|----|

Materials

| | |
|---------------------|-------------|
| Colour of labelling | 217,217,217 |
|---------------------|-------------|

| | |
|-----------------------|----------------------|
| Colour of design line | aluminium/anthracite |
|-----------------------|----------------------|

| | |
|------------------------------------|------------------------------|
| Colour independent of design lines | for anthracite and aluminium |
|------------------------------------|------------------------------|

| | |
|-----------------------|-------|
| Material for printing | Paper |
|-----------------------|-------|

| | |
|--------------------|--------|
| Surface appearance | glossy |
|--------------------|--------|

| | |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

| | |
|-----------------|---------|
| Material family | Plastic |
|-----------------|---------|

LED control

| | |
|-----|--|
| LED | with white operation LED and 8 red status LEDs |
|-----|--|

Connection

| | |
|-------------------|-------------------------------------|
| Bus coupling unit | for bus coupling unit flush-mounted |
|-------------------|-------------------------------------|

| | |
|--|---|
| Settings | |
| Parameterisation | single and two push-button operation parameterisable |
| Scope of delivery | |
| Bus connection included | No |
| Equipment | |
| Number of actuation points | 8 |
| With anti-theft/dismantling protection | Yes |
| Type of configuration | Beschriftungsfeld(er) - Folie |
| Product type: | product type: push-button 4gang |
| Use | |
| Differentiation characteristic 1 - Sales | with labelling fields |
| Differentiation characteristic 3 - Sales | with horizontal operation |
| Safety | |
| Protection | with dismantling protection |
| Alarm | alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte |
| Use conditions | |
| Operating temperature | -5...45 °C |
| Identification | |
| Application, usage | KNX - operating systems |
| Product family | product family: push-button |
| Secondary design line(s) | KNX ; Berker S.1 ; Berker B.3 ; Berker B.7 |
| Instructions | |
| Special note text | Use only in combination with frame frame with large cut-out. |