




80163773

IP20



**Push-button 3gang, lab. field,+RGB LED, int. temp. sensor, KNX-K.5, stainl.steel**

**Technical properties**

**Functions**

With room temperature controller Yes

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; Orientation LED can be controlled via object ; brightness value of the status LED for day/nighttime operation preset, status LED for day/nighttime operation can be controlled via object ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, temperature setpoint adjustment, operating mode changeover

Easy link functions

Function Function for manual interruption of automatic functions already triggered

operating surfaces as buttons (single-surface operation) and rockers (two-surface operation) ; the brightness of status LEDs are individually adjustable for button/ rocker function ; brightness value of the status LEDs for day/nighttime operation adjustable via object or manually ; value transmitter for dimming, position, brightness temperature values 1 and 2 byte ; button/rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, automatic control deactivation ; integrated temperature sensor with output of the measured values via object ; button functions for switching, dimming, roller shutter/blind, timer, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, 2-channel mode, step switch, automatic control deactivation ; rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, 2-channel mode, automatic control deactivation ; 3-step switch, function for incremental selection of up to 7 stored values ; parameter definable lock function ; Status LED configurable in its colour per button

Function

**Controls and indicators**

With LED indication Yes

Number of buttons 3

Operation operating areas configurable as one or two-area operation

**Electric current**

Bus current consumption (data transfer) max. 20 mA

**Dimensions**

Labelling field length (W x H) 66.8 x 15.7 mm

Height 15.7 mm

Width 66 mm

<b>Power</b>	
Power consumption, KNX	≈ 150 mW
<b>Measurement</b>	
Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
<b>Screen</b>	
With display	No
<b>Materials</b>	
Material for printing	Paper
Material family	Plastic
<b>LED control</b>	
LED	with white operating LED ; with 2 RGB status LEDs per rocker
<b>Connection</b>	
Bus coupling unit	for bus coupling unit flush-mounted
<b>Settings</b>	
Supported configuration modes	system, easy
Parameterisation	single and two push-button operation parameterisable
<b>Scope of delivery</b>	
Bus connection included	No
<b>Equipment</b>	
Number of actuation points	6
With anti-theft/dismantling protection	Yes
Product type:	product type: push-button 3gang
<b>Use</b>	
Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 2 - Sales	and RGB LED
Differentiation characteristic 3 - Sales	with integrated temperature sensor
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
Temperature	integrated temperature sensor with output of the measured values via object

**Identification**

---

Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX ; Berker K.1 ; Berker K.5

---

**Instructions**

---

Special note text	Use only in conjunction with bus coupling unit 8004 00 01!
-------------------	---

---