



75261259



KNX cont. 2.2 m, KNX - S.1, p. white glossy

Technical properties

Functions

Function parameter defineable lock function

Compatibility

Extension unit also suitable as extension unit

Controls and indicators

Number of switching segments 72

Dimensions

Dimensions assembling height 23.5 mm

Nominal mounting height 2.2 m

Measurement

Detection field, semi-oval shaped $\approx 12 \times 12 \text{ m}$

Reach distance

Range, frontal $\approx 12 \text{ m}$

Range, frontal (at 1.1 m installation height) $\approx 6 \text{ m}$

Range, side each $\approx 6 \text{ m}$

Range, side (at 1.1 m installation height) each $\approx 3 \text{ m}$

Cover, door

Cover with cover to limit detection angle to 90°

Detection

Number of detection levels 2

Detection angle 180°

Sensor type detector of movement

Materials

Colour of design line polar white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

Lighting control

Response brightness, configurable 1...1000 lx / daytime operation

Connection

Bus coupling unit for bus coupling unit flush-mounted

Settings

Supported configuration modes	system
Response sensitivity, settable	20...100 %
Delay time	≈ 10 s
Additional delay time programmable	130 ms...152 h
Setting	with potentiometer for fine adjustment of the response sensitivity

Equipment

Product type:	product type: movement
---------------	------------------------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - sensors
Product family	product family: physical sensors
Main design line	KNX - Berker S.1/B.3/B.7
Secondary design line(s)	KNX ; Motion detector

Instructions

Information text	Application as for order no. 7526 11 ..
------------------	-----------------------------------------