




80164773



**Push-button 4gang, lab. field,+RGB LED, int. temp. sensor, KNX-K.5, stainl.steel**

**Technical properties**

**Architecture**

Fixing mode flush-mounting

**Functions**

With room temperature controller Yes

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; Orientation LED can be controlled via object ; brightness value of the status LED for day/nighttime operation preset, status LED for day/nighttime operation can be controlled via object ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, temperature setpoint adjustment, operating mode changeover

Easy link functions

**Controls and indicators**

With LED indication Yes

Number of buttons 4

**Electric current**

Bus current consumption (data transfer) max. 20 mA

**Dimensions**

Labelling field length (W x H) 66.8 x 25 mm

Height 25 mm

Width 66.8 mm

**Power**

Power consumption, KNX ≈ 150 mW

**Measurement**

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

**Screen**

With display No

**Materials**

Material thermoplastic

Material for printing Paper

Material family Plastic

**Connection**

**Settings**

Supported configuration modes system

Parameterisation single and two push-button operation parameterisable

**Scope of delivery**

Bus connection included No

**Equipment**

Number of actuation points 8

With anti-theft/dismantling protection Yes

Product type: product type: push-button 4gang

**Use cases**

Frame only for frame with large cut-out

**Use**

Differentiation characteristic 1 - Sales with labelling fields

**Safety**

Protection index IP IP20

Protection with dismantling protection

Alarm alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

**Use conditions**

Operating temperature -5...45 °C

Storage/transport temperature -20...70 °C (storage at &gt; 45°C reduces the service life)

**Identification**

Application, usage KNX - operating systems

Product family product family: push-button

Secondary design line(s) KNX, Berker K.1, Berker K.5

**Instructions**

Special note text In the design lines S.1/B.x and K.x only to be used in combination with a frame with a large cut-out! ; Use only in conjunction with bus coupling unit 8004 00 01!