



75261273

KNX cont. 2.2 m, KNX - K.5, stainless steel matt, lacq.

Technical properties

Functions

Function	parameter defineable lock function
----------	------------------------------------

Compatibility

Extension unit	also suitable as extension unit
----------------	---------------------------------

Controls and indicators

Number of switching segments	72
------------------------------	----

Dimensions

Dimensions assembling height	23.5 mm
Nominal mounting height	2.2 m

Measurement

Detection field, semi-oval shaped	≈ 12 x 12 m
-----------------------------------	-------------

Reach distance

Range, frontal	≈ 12 m
Range, frontal (at 1.1 m installation height)	≈ 6 m
Range, side	each ≈ 6 m
Range, side (at 1.1 m installation height)	each ≈ 3 m

Cover, door

Cover	with cover to limit detection angle to 90°
-------	--

Detection

Number of detection levels	2
Detection angle	180 °
Sensor type	detector of movement

Materials

Colour of design line	stainless steel
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

Lighting control

Response brightness, configurable	1...1000 lx / daytime operation
-----------------------------------	---------------------------------

Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

Settings

Supported configuration modes	system
Response sensitivity, settable	20...100 %
Delay time	≈ 10 s
Additional delay time programmable	130 ms...152 h
Setting	with potentiometer for fine adjustment of the response sensitivity

Equipment

Product type:	product type: movement
---------------	------------------------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - sensors
Product family	product family: physical sensors
Main design line	KNX - Berker K.5
Secondary design line(s)	KNX, Berker K.5, Motion detector

Instructions

Information text	Application as for order no. 7526 11 ..
------------------	---