



75261659



**KNX cont. comf 2.2 m, KNX - S.1, p. white glossy**

## Technical properties

### Architecture

Fixing mode	flush-mounting
-------------	----------------

### Functions

Max. temporisation	306 h
--------------------	-------

Potentiometer for additional delay time	± 50 %
---	--------

### Function

Functions for lighting operating mode: Switching, Value transmitter and Light scene call ; parameter defineable lock function

Slide switch	with slide switch for OFF/automatic/ON
--------------	--

### Compatibility

Extension unit	also suitable as extension unit
----------------	---------------------------------

### Controls and indicators

Number of switching segments	72
------------------------------	----

### Dimensions

Dimensions assembling height	23.5 mm
------------------------------	---------

Nominal mounting height	2.2 m
-------------------------	-------

Optimum mounting height	2.2 m
-------------------------	-------

### Power

Power consumption, KNX	≈ 110 mW
------------------------	----------

### Measurement

Detection field, semi-oval shaped	≈ 12 x 12 m
-----------------------------------	-------------

### Reach distance

Range, frontal	≈ 12 m
----------------	--------

Range, frontal (at 1.1 m installation height)	≈ 6 m
---	-------

Range, side	each ≈ 6 m
-------------	------------

Range, side (at 1.1 m installation height)	each ≈ 3 m
--	------------

Max. transmission range frontally	12 m
-----------------------------------	------

Max. transmission range sideways	6 m
----------------------------------	-----

### Cover, door

Cover	with cover to limit detection angle to 90°
-------	--

### Detection

Number of detection levels	2
----------------------------	---

Detection angle	180 °
-----------------	-------

Detection angle vertical	0 / 7 °
Detection angle horizontal	0 / 180 °
Sensor type	detector of movement
<b>Materials</b>	
Colour of design line	polar white
<b>Lighting control</b>	
Response brightness, configurable	3...100 lx / daytime operation
<b>LED control</b>	
LED	with red diagnostic LED for brightness-independent walk test function and disassembly message
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	0 W
<b>Connection</b>	
Bus coupling unit	for bus coupling unit flush-mounted
<b>Settings</b>	
Supported configuration modes	system
Response brightness adjustable by potentiometer	± 50 %
Response sensitivity, settable	20...100 %
Min. temporisation	130 ms
Delay time	≈ 10 s
Additional delay time programmable	130 ms...306 h
Setting	with potentiometers for fine adjustment of the response brightness, sensitivity and delay time
<b>Equipment</b>	
Product type:	product type: movement
<b>Safety</b>	
Protection index IP	IP20
Alarm	alarm telegram after disconnection from bus coupling unit, 1-bit
<b>Use conditions</b>	
Operating temperature	-5...45 °C
<b>Identification</b>	
Application, usage	KNX - sensors
Product family	product family: physical sensors
Main design line	KNX - Berker S.1
Secondary design line(s)	Motion detector ; KNX
<b>Instructions</b>	
Information text	Application as for order no. 7526 15 .. Caution: Direct sunlight can lead to false alarms when using alarm application. Avoid using detection field equipment on windows.