



75441179



Thermostat with push-button interface, K.1, polar white glossy

Technical properties

Functions

Operating mode operating modes: comfort, standby, night lowering, frost/heat protection, dewpoint displayed with LED

Controls and indicators

Button / push-button presence button and setting knob can be programmed to have no functions ; with programming button and red programming LED ; with presence button for switching between comfort and standby mode

Connectivity

Binary inputs with 4 independent binary inputs for potential-free contacts e.g. window magnetic contact ; 4 binary inputs or 2-3 binary inputs and 1-2 outputs parameterisable

Voltage

Operating voltage over bus 21...32 V DC

Electric current

Bus current consumption (data transfer) ≈ 10 mA

Output current per channel max. 0.8 mA

Materials

Colour of design line polar white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

Type of surface treatment untreated

LED control

LED with status LEDs: red for heating, blue for cooling and yellow for activation

Installation, mounting

Installation mode without spreader claws

Connection

Sensor cable length 50 m

Conductor cross-section (flexible) 0.3...1 mm²

Conductor cross-section (rigid) 1.5 mm²

Type of connection Binary inputs / outputs with screw terminals

Bus connection bus connection via connecting terminal

Cable

Cable length, inputs/outputs

max. 5 m

Settings

Supported configuration modes system

Parameterisation valve protection can be defined ; conduct can be defined for bus voltage return

Equipment

Product type: product type: thermostat

Set value control by setting knob $\pm 0...5$ K

Heating for heating and/or cooling mode ; heating or cooling possible in 2 stages

Control for continuous (PI) or switched (2-point) control ; for individual single room temperature control

Use

Differentiation characteristic 2 - Sales with setting knob

Differentiation characteristic 3 - Sales with integral bus coupling unit

Safety

REACH conform Yes

RoHS conform Yes

Protection with dismantling protection

Use conditions

Operating temperature $-5...45$ °C

Energy efficiency class IV (2%)

Identification

Application, usage KNX - sensors

Product family Product family: heating, ventilation, air conditioning

Main design line KNX - Berker K.1/K.5

Secondary design line(s) KNX ; Berker K.1

Instructions

Special note text Binary input 4 parameter defineable for temperature sensor, order no. 161.