



75441271

IP20



KNX object thermostat, intg bus coupling unit, KNX - K.5, al., al. anodised

Technical properties

Functions

Operating mode operating modes: comfort, standby, night lowering, frost/heat protected, dewpoint

Controls and indicators

Button / push-button with programming button and red programming LED

Connectivity

Binary inputs with 4 independent binary inputs for potential-free contacts e.g. window magnetic contact ; 4 binary inputs or 2-3 binary inputs and 1-2 outputs parameterisable

Voltage

Operating voltage over bus 21...32 V DC

Electric current

Bus current consumption (data transfer) max. 7.5 mA

Output current per channel max. 0.8 mA

Materials

Colour of design line Aluminium

Material / workmanship aluminium, anodised

Surface appearance matt

Installation, mounting

Installation mode without spreader claws

Connection

Sensor cable length 50 m

Conductor cross-section (flexible) 0.3...1 mm²

Conductor cross-section (rigid) 1.5 mm²

Type of connection Binary inputs / outputs with screw terminals

Bus connection bus connection via connecting terminal

Cable

Cable length, inputs/outputs max. 5 m

Settings

Supported configuration modes system

Parameterisation conduct can be defined for bus voltage return ; valve protection can be defined

Equipment

Product type:	product type: thermostat
Heating	for heating and/or cooling mode ; heating or cooling possible in 2 stages
Control	for continuous (PI) or switched (2-point) control ; for single room control
Use	
Differentiation characteristic 3 - Sales	with integral bus coupling unit
Safety	
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Energy efficiency class	IV (2%)
Identification	
Application, usage	KNX - sensors
Product family	Product family: heating, ventilation, air conditioning
Main design line	KNX - Berker K.1/K.5
Secondary design line(s)	KNX ; Berker K.1 ; Berker K.5
Instructions	
Special note text	Binary input 4 parameter defineable for temperature sensor, order no. 161.