



75441272

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Operating mode operating modes: comfort, standby, night lowering, frost/heat protected, dewpoint

Controls and indicators

Button / push-button with programming button and red programming LED

Connectivity

Binary inputs with 4 independent binary inputs for potential-free contacts e.g. window magnetic contact, 4 binary inputs or 2-3 binary inputs and 1-2 outputs parameterisable

Voltage

Operating voltage over bus 21...32 V DC

Electric current

Bus current consumption (data transfer) max. 7.5 mA

Output current per channel max. 0.8 mA

Materials

Colour of design line white

RAL colour RAL 1013 - Oyster white

Material Plastic/metal

Type of surface treatment untreated

Installation, mounting

Installation mode without spreader claws

Connection

Sensor cable length 50 m

Conductor cross-section (flexible) 0.3...1 mm²

Conductor cross-section (rigid) 1.5 mm²

Type of connection Binary inputs / outputs with screw terminals

Bus connection bus connection via connecting terminal

Cable

Cable length, inputs/outputs max. 5 m

Settings

Supported configuration modes system

Parameterisation

conduct can be defined for bus voltage return, valve protection can be defined

Equipment

Product type:

product type: thermostat

Heating

for heating and/or cooling mode, heating or cooling possible in 2 stages

Control

for continuous (PI) or switched (2-point) control, for single room control

Use

Differentiation characteristic 3 - Sales

with integral bus coupling unit

Safety

Protection

with dismantling protection

Use conditions

Operating temperature

-5...45 °C

Energy efficiency class

IV (2%)

Identification

Application, usage

KNX - sensors

Product family

Product family: heating, ventilation, air conditioning

Secondary design line(s)

KNX

Instructions

Special note text

Binary input 4 parameter defineable for temperature sensor, order no. 161.