



80960329

IP20



Cover for 2gang for push-button module, clearlenses, Q.x, p. white velvety

Technical properties

Functions

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; brightness value of the status LED for day/nighttime operation preset, change-over for day/nighttime operation possible ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, operating mode changeover

Easy link functions

Function Function for manual interruption of automatic functions already triggered

Function operating surfaces as buttons (single-surface operation) and rockers (two-surface operation) ; the brightness of status LEDs are individually adjustable for button/ rocker function ; brightness value of the status LEDs for day/nighttime operation adjustable via object or manually ; value transmitter for dimming, position, brightness temperature values 1 and 2 byte ; integrated temperature sensor with output of the measured values via object ; parameter defineable lock function ; button/rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, automatic control deactivation

Controls and indicators

Operation operating areas configurable as one or two-area operation
 Button / push-button with programming button and red programming LED

Voltage

Operating voltage over bus 21...32 V DC

Dimensions

Height 58 mm

Power

Power consumption, KNX ≈ 108 mW

Camera

Lens with 2 clear lenses for the RGB status display of the push-button module

Materials

Colour of design line polar white
 RAL colour RAL 9010 - Pure white
 Material / workmanship lacquered

Surface appearance

velvety

Connection

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

Settings

Supported configuration modes system, easy

Equipment

Buzzer/siren with integrated buzzer for acoustic identification of the device within the system

Use

Differentiation characteristic 2 - Sales with clear lens

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C

Storage/transport temperature -20...70 °C (storage at > 45°C reduces the service life)

Temperature integrated temperature sensor with output of the measured values via object

Identification

Application, usage KNX - operating systems

Product family product family: push-button

Main design line KNX - Berker Q.1/Q.3

Secondary design line(s) KNX ; Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9