



75441273

IP20



KNX object thermostat, intg bus coupl. unit, KNX-K.5, steel, metal matt finish

Technical properties

Functions

| | |
|----------------|---|
| Operating mode | operating modes: comfort, standby, night lowering, frost/heat protected, dewpoint |
|----------------|---|

Controls and indicators

| | |
|----------------------|---|
| Button / push-button | with programming button and red programming LED |
|----------------------|---|

Connectivity

| | |
|---------------|--|
| Binary inputs | with 4 independent binary inputs for potential-free contacts e.g. window magnetic contact ; 4 binary inputs or 2-3 binary inputs and 1-2 outputs parameterisable |
|---------------|--|

Voltage

| | |
|----------------------------|--------------|
| Operating voltage over bus | 21...32 V DC |
|----------------------------|--------------|

Electric current

| | |
|---|-------------|
| Bus current consumption (data transfer) | max. 7.5 mA |
| Output current per channel | max. 0.8 mA |

Materials

| | |
|---------------------------|--------------------|
| Colour of design line | Stainless steel |
| Material / workmanship | metal, matt finish |
| Surface appearance | matt |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|-------------------|------------------------|
| Installation mode | without spreader claws |
|-------------------|------------------------|

Connection

| | |
|------------------------------------|--|
| Sensor cable length | 50 m |
| Conductor cross-section (flexible) | 0.3...1 mm ² |
| Conductor cross-section (rigid) | 1.5 mm ² |
| Type of connection | Binary inputs / outputs with screw terminals |
| Bus connection | bus connection via connecting terminal |

Cable

| | |
|------------------------------|----------|
| Cable length, inputs/outputs | max. 5 m |
|------------------------------|----------|

Settings

| | |
|-------------------------------|---|
| Supported configuration modes | system |
| Parameterisation | conduct can be defined for bus voltage return ; valve protection can be defined |

Equipment

| | |
|---------------|--------------------------|
| Product type: | product type: thermostat |
|---------------|--------------------------|

| | |
|---------|---|
| Heating | for heating and/or cooling mode ; heating or cooling possible in 2 stages |
|---------|---|

| | |
|---------|---|
| Control | for continuous (PI) or switched (2-point) control ; for single room control |
|---------|---|

Use

| | |
|--|---------------------------------|
| Differentiation characteristic 3 - Sales | with integral bus coupling unit |
|--|---------------------------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|------------|-----------------------------|
| Protection | with dismantling protection |
|------------|-----------------------------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...45 °C |
|-----------------------|------------|

| | |
|-------------------------|---------|
| Energy efficiency class | IV (2%) |
|-------------------------|---------|

Identification

| | |
|--------------------|---------------|
| Application, usage | KNX - sensors |
|--------------------|---------------|

| | |
|----------------|--|
| Product family | Product family: heating, ventilation, air conditioning |
|----------------|--|

| | |
|------------------|----------------------|
| Main design line | KNX - Berker K.1/K.5 |
|------------------|----------------------|

| | |
|--------------------------|-------------------------------|
| Secondary design line(s) | KNX ; Berker K.1 ; Berker K.5 |
|--------------------------|-------------------------------|

Instructions

| | |
|-------------------|--|
| Special note text | Binary input 4 parameter defineable for temperature sensor, order no. 161. |
|-------------------|--|
