



75441273

IP20



## KNX object thermostat, intg bus coupl. unit, KNX-K.5, steel, metal matt finish

### Technical properties

#### Functions

Operating mode	operating modes: comfort, standby, night lowering, frost/heat protected, dewpoint
----------------	---

#### Controls and indicators

Button / push-button	with programming button and red programming LED
----------------------	---

#### Connectivity

Binary inputs	with 4 independent binary inputs for potential-free contacts e.g. window magnetic contact ; 4 binary inputs or 2-3 binary inputs and 1-2 outputs parameterisable
---------------	--

#### Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

#### Electric current

Bus current consumption (data transfer)	max. 7.5 mA
Output current per channel	max. 0.8 mA

#### Materials

Colour of design line	Stainless steel
Material / workmanship	metal, matt finish
Surface appearance	matt
Type of surface treatment	untreated

#### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

#### Connection

Sensor cable length	50 m
Conductor cross-section (flexible)	0.3...1 mm <sup>2</sup>
Conductor cross-section (rigid)	1.5 mm <sup>2</sup>
Type of connection	Binary inputs / outputs with screw terminals
Bus connection	bus connection via connecting terminal

#### Cable

Cable length, inputs/outputs	max. 5 m
------------------------------	----------

#### Settings

Supported configuration modes	system
Parameterisation	conduct can be defined for bus voltage return ; valve protection can be defined

**Equipment**

---

Product type: product type: thermostat

---

Heating for heating and/or cooling mode ; heating or cooling possible in 2 stages

---

Control for continuous (PI) or switched (2-point) control ; for single room control

**Use**

---

Differentiation characteristic 3 - Sales with integral bus coupling unit

**Safety**

---

REACH conform Yes

---

RoHS conform Yes

---

Protection with dismantling protection

**Use conditions**

---

Operating temperature -5...45 °C

---

Energy efficiency class IV (2%)

**Identification**

---

Application, usage KNX - sensors

---

Product family Product family: heating, ventilation, air conditioning

---

Main design line KNX - Berker K.1/K.5

---

Secondary design line(s) KNX ; Berker K.1 ; Berker K.5

**Instructions**

---

Special note text Binary input 4 parameter defineable for temperature sensor, order no. 161.