




75642039



Technical properties

Functions

With room temperature controller	Yes
Function	with valve protection function ; for switch, push-button, dimmer, blind and thermostat functions
Operating mode	controller operating modes: comfort, standby, night and frost/heat protection mode

Controls and indicators

With LED indication	Yes
Number of buttons	0
Operation	operation by gently touching the sensor surfaces on the white LED
Indication / display	LED display with symbol display ; display of operating mode, controller lockout, room/outside temperature, time (clock required)
Button / push-button	with 2 additional display sensor surfaces

Connectivity

Encoding	with button blocking function
----------	-------------------------------

Voltage

Voltage	operation with non-choked output of KNX voltage supply possible (pay attention to current consumption) ; separate auxiliary power supply needed
---------	---

Dimensions

Depth	5.7 mm
Depth	5.7 mm
Dimensions (W x H x D)	86 x 160 x 5.7 mm
Height	160 mm
Width	86 mm

Power

Current consumption	23 mA
---------------------	-------

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	Yes
--------------	-----

Materials

Colour of design line	glass polar white
RAL colour	RAL 9010 - Pure white

Surface appearance	glossy
Material family	Glass
LED control	
LED	with blue operation LED and 4 white status LEDs
Installation, mounting	
Installation mode	for vertical mounting
Connection	
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Settings	
Parameterisation	single and two push-button operation parameterisable ; end customer display scope parameterisable
Scope of delivery	
Bus connection included	Yes
Accessories included	
Adapters	with adapter ring for dismantling protection and shadow gap formation
Matching products	for glass frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x
Equipment	
Number of actuation points	4
With anti-theft/dismantling protection	Yes
Heating	for heating and/or cooling mode with/without auxiliary step
Control	for individual single room temperature control ; control parameter for heating / cooling unit pre-set ; for continuous (PI) or switched (2-point) control
Use	
Differentiation characteristic 2 - Sales	Display
Differentiation characteristic 3 - Sales	integrated bus coupling unit
Use conditions	
Operating temperature	-5...45 °C
Temperature	additional connection for external temperature sensor ; temperature measurement via internal temperature sensor or external communication object
Energy efficiency class	IV (2%)
Identification	
Main design line	KNX - Berker TS Sensor
Secondary design line(s)	Berker TS Sensor ; KNX
Instructions	
Information text	Only suitable for KNX.