




75643135



KNX glass sensor 3g thermostat, display, intg bus coupl. , KNX-TS sensor, bl.

Technical properties

Functions

With room temperature controller Yes

Function with valve protection function ; for switch, push-button, dimmer, blind and thermostat functions

Operating mode controller operating modes: comfort, standby, night and frost/heat protection mode

Controls and indicators

With LED indication Yes

Operation operation by gently touching the sensor surfaces on the white LED

Indication / display LED display with symbol display ; display of operating mode, controller lockout, room/outside temperature, time (clock required)

Button / push-button with 2 additional display sensor surfaces

Connectivity

Encoding with button blocking function

Voltage

Voltage operation with non-choked output of KNX voltage supply possible (pay attention to current consumption) ; separate auxiliary power supply needed

Dimensions

Depth 37.7 mm

Depth 5.7 mm

Dimensions (W x H x D) 86 x 160 x 5.7 mm

Height 160 mm

Width 86 mm

Power

Current consumption 23 mA

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display Yes

Materials

Colour of labelling 217,217,217

Colour of design line glass black

LED control

LED	with blue operation LED and 6 white status LEDs
-----	---

Installation, mounting

Installation mode	for vertical mounting
-------------------	-----------------------

Connection

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

Bus connection	bus connection via connecting terminal
----------------	--

Settings

Parameterisation	single and two push-button operation parameterisable ; end customer display scope parameterisable
------------------	---

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Accessories included

Adapters	with adapter ring for dismantling protection and shadow gap formation
----------	---

Matching products	for glass frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x
-------------------	--

Equipment

With anti-theft/dismantling protection	Yes
--	-----

Type of configuration	Laserdruck
-----------------------	------------

Heating	for heating and/or cooling mode with/without auxiliary step
---------	---

Control	for individual single room temperature control ; control parameter for heating / cooling unit pre-set ; for continuous (PI) or switched (2-point) control
---------	---

Use

Differentiation characteristic 2 - Sales	Display
--	---------

Differentiation characteristic 3 - Sales	integrated bus coupling unit
--	------------------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Temperature	additional connection for external temperature sensor ; temperature measurement via internal temperature sensor or external communication object
-------------	--

Energy efficiency class	IV (2%)
-------------------------	---------

Identification

Application, usage	KNX - operating systems
--------------------	-------------------------

Main design line	KNX - Berker TS Sensor - configured
------------------	-------------------------------------

Instructions

Information text

Only suitable for KNX.