




80960379

IP20



**Cover for 2gang for push-button module, clearlenses, K.1, p. white glossy**

**Technical properties**

**Functions**

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; brightness value of the status LED for day/nighttime operation preset, change-over for day/nighttime operation possible ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, operating mode changeover

Easy link functions

Function Function for manual interruption of automatic functions already triggered

Function operating surfaces as buttons (single-surface operation) and rockers (two-surface operation) ; the brightness of status LEDs are individually adjustable for button/ rocker function ; brightness value of the status LEDs for day/nighttime operation adjustable via object or manually ; value transmitter for dimming, position, brightness temperature values 1 and 2 byte ; integrated temperature sensor with output of the measured values via object ; parameter defineable lock function ; button/rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, automatic control deactivation

**Controls and indicators**

Operation operating areas configurable as one or two-area operation  
 Button / push-button with programming button and red programming LED

**Voltage**

Operating voltage over bus 21...32 V DC

**Dimensions**

Height 55 mm

**Power**

Power consumption, KNX ≈ 108 mW

**Camera**

Lens with 2 clear lenses for the RGB status display of the push-button module

**Materials**

Colour of design line polar white  
 RAL colour RAL 9010 - Pure white  
 Surface appearance glossy

Type of surface treatment

untreated

### Connection

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

### Settings

Supported configuration modes system, easy

### Equipment

Buzzer/siren with integrated buzzer for acoustic identification of the device within the system

### Use

Differentiation characteristic 2 - Sales with clear lens

### Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection with dismantling protection

### Use conditions

Operating temperature -5...45 °C

Storage/transport temperature -20...70 °C (storage at > 45°C reduces the service life)

Temperature integrated temperature sensor with output of the measured values via object

### Identification

Application, usage KNX - operating systems

Product family product family: push-button

Main design line KNX - Berker K.1/K.5

Secondary design line(s) KNX ; Berker K.1 ; Berker K.5