



85221100

## Blind insert comf, electronics

### Technical properties

#### Functions

Power reserve 0 h

#### Configuration

Switch mode with 2 mechanically and electrically mutually-locked relay contacts

#### Main electrical features

Frequency 50/60 Hz

#### Electric current

Switching current (ohmic/inductive) max. 5 A

Switching current at  $\cos \varphi = 0.6$  max. 3 A

#### Dimensions

Insertion depth 32 mm

Claw guidance installation depth 32 mm

Housing installation depth 22 mm

#### Measurement

Extension unit input with 230 V extension unit inputs for up and down

#### Materials

Material / surface no conductive connection between supporting ring and spreading claws

#### Lighting control

Twilight setting range 0 lx

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Screw terminals (max.) 2 x 1,5/1 x 2,5 mm<sup>2</sup>

Type of connection with screw terminals

Number of substations unlimited

Connection circuiting of extension units push-buttons for blinds, blind inserts, key push-buttons for blinds

#### Cable

Load cable length max. 100 m

Cable length, extensions max. 50 m

**Equipment**

---

Change-over time for change of direction	< 0.6 s
--	---------

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

Energy-saving	low intrinsic energy requirement
---------------	----------------------------------

---

Relative humidity (without condensation)	0...65 % (without condensation)
--	---------------------------------

**Identification**

---

Application, usage	Blind control ; KNX radio- operating systems
--------------------	--

---

Main design line	Electronics platform
------------------	----------------------