



75663693



B.IQ IR Push Button with Thermostat, 3-Gang, Brushed Stainless Steel

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Function with valve protection function

Timers with room temperature timer and 2-week timer functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

Number of buttons 3

Operation one push-button operation for switching, pushing, shutters and dimming

Dimensions

Height 128.6 mm

Width 88.5 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Materials

Colour of design line Stainless steel

RAL colour RAL 9022 - Pearl light grey

Material / workmanship metal brushed

Material stainless steel

Surface appearance matt

Type of surface treatment brushed

LED control

LED with blue operation LED and 6 white status LEDs (labelling field illumination)

Settings

Parameterisation single and two push-button operation parameterisable

Scope of delivery

Bus connection included No

Accessories included

| | |
|----------------------------|---|
| Box | for installation in single standard wall boxes |
| Matching products | for stainless steel frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x |
| Equipment | |
| Number of actuation points | 8 |
| Product type: | product type: B.IQ |
| Control | for individual single room temperature control |
| Software | |
| Update | with flash-controller technology |
| Safety | |
| Protection | with dismantling protection |
| Use conditions | |
| Operating temperature | -5...45 °C |
| Energy efficiency class | IV (2%) |
| Identification | |
| Application, usage | KNX - operating systems |
| Product family | product family: push-button |
| Release issue | 2.6 |
| Main design line | KNX - Berker B.IQ |
| Secondary design line(s) | Berker B.IQ, KNX |
| Instructions | |
| Information text | IR hand-held transmitter, order no. 2779 |