




75663770



Push-button 3gang with room thermostat, display, K.1

Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller Yes

Function with valve protection function

Timers with room temperature timer

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 3

Operation one push-button operation for switching, pushing, shutters and dimming

Dimensions

Labelling field length (W x H) 66.8 x 24.9 mm

Height 111.1 mm

Width 70.9 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display Yes

Materials

Colour of design line polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material thermoplastic

Material for printing Paper

Type of surface treatment untreated

LED control

LED with white operation LED and 6 red status LEDs

Connection

Bus coupling unit for bus coupling unit flush-mounted

Settings	
Parameterisation	single and two push-button operation parameterisable
Scope of delivery	
Bus connection included	No
Equipment	
Number of actuation points	8
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 3gang
Control	for individual single room temperature control
Software	
Update	with flash-controller technology
Safety	
Protection index IP	IP20
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
Use conditions	
Operating temperature	-5...45 °C
Energy efficiency class	IV (2%)
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker K.1/K.5
Secondary design line(s)	KNX, Berker K.1
Instructions	
Special note text	Use only in combination with frame frame with large cut-out.