



85241131

Shutter push-button, R.1/R.3/1930/R.cl., black glossy

Technical properties

Functions

Venetian blind movement time	2 mn
Running time	max. 2 mn

Main electrical features

Nominal voltage	12 V
Frequency	- Hz

Dimensions

Diameter	57.6 mm
----------	---------

Materials

Colour of design line	black
Colour	black
Material	thermoplastic

Installation, mounting

Installation mode	clamp fastening
-------------------	-----------------

Settings

Lamella adjusting time	(adjustable) 50 ms...2.5 s
Minimum slat adjustment time	≈ 250 ms
Delay time, adjustable	0...500 s
Lamella adjustment on button-press	< 0.4 s

Equipment

Self-retaining for 2 min on button-press	> 0.4 s
Change-over time for change of direction	< 0.6 s

Safety

Protection	with dismantling protection
------------	-----------------------------

Use conditions

Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Blind control
Main design line	Berker R.1/R.3/R.8/Serie 1930/R.classic
Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8

Instructions

Can be switched to orientation led by extension unit.
; Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!

Special note text