



85241179

## Shutter push-button, K.1, p. white glossy

### Technical properties

#### Functions

Venetian blind movement time	2 mn
------------------------------	------

#### Main electrical features

Nominal voltage	12 V
Frequency	- Hz

#### Detection

Sensor	Not suitable for rain and wind sensors
--------	--

#### Materials

Colour of design line	polar white
Colour	polarwhite
Material	thermoplastic

#### Installation, mounting

Installation mode	clamp fastening
-------------------	-----------------

#### Settings

Lamella adjusting time	(adjustable) 50 ms...2.5 s
Minimum slat adjustment time	≈ 250 ms
Delay time, adjustable	0...500 s
Lamella adjustment on button-press	< 0.4 s

#### Equipment

Self-retaining for 2 min on button-press	> 0.4 s
Change-over time for change of direction	< 0.6 s

#### Safety

Halogen free	No
Protection	with dismantling protection

#### Use conditions

Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)

#### Identification

Application, usage	Blind control
Main design line	Berker K.1
Secondary design line(s)	Berker K.1

