



75663785



S.1/B.3/B.7 Push Button 3-gang, Thermostat/Label, Anthracite/Aluminium

Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller Yes

Function with valve protection function

Timers with room temperature timer

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 3

Operation one push-button operation for switching, pushing, shutters and dimming

Dimensions

Labelling field length (W x H) 52.3 x 24.9 mm

Height 110.8 mm

Width 55.8 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display Yes

Materials

Colour of labelling 217,217,217

Colour independent of design lines for anthracite and aluminium

Colour other

RAL colour RAL 7021 - Black grey

Material thermoplastic

Material for printing Paper

Type of surface treatment untreated

LED control

LED with white operation LED and 6 red status LEDs

Connection

Settings

| | |
|------------------|--|
| Parameterisation | single and two push-button operation parameterisable |
|------------------|--|

Scope of delivery

| | |
|-------------------------|----|
| Bus connection included | No |
|-------------------------|----|

Equipment

| | |
|--|--|
| Number of actuation points | 8 |
| With anti-theft/dismantling protection | Yes |
| Type of configuration | Beschriftungsfeld(er) - Folie |
| Product type: | product type: push-button 3gang |
| Control | for individual single room temperature control |

Software

| | |
|--------|----------------------------------|
| Update | with flash-controller technology |
|--------|----------------------------------|

Safety

| | |
|---------------------|---|
| Protection index IP | IP20 |
| Protection | with dismantling protection |
| Alarm | alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte |

Use conditions

| | |
|-------------------------|------------|
| Operating temperature | -5...45 °C |
| Energy efficiency class | IV (2%) |

Identification

| | |
|--------------------------|---|
| Application, usage | KNX - operating systems |
| Product family | product family: push-button |
| Main design line | KNX - Berker S.1/B.3/B.7 |
| Secondary design line(s) | KNX, Berker S.1, Berker B.3, Berker B.7 |

Instructions

| | |
|-------------------|--|
| Special note text | Use only in combination with frame frame with large cut-out. |
|-------------------|--|