



85341129

**Motion det. 1.1 m, Q.x, p. white velvety**

**Technical properties**

**Architecture**

Fixing mode flush-mounting

**Functions**

Function with keylock

**Controls and indicators**

Button / push-button with button for on/off/automatic

**Dimensions**

Assembling height 34 mm

Nominal mounting height 1.1 m

**Measurement**

Detection field, rectangular shaped  $\approx 12 \times 16$  m

**Reach distance**

Range, frontal  $\approx 12$  m

**Detection**

Number of detection levels 3

Detection angle, settable each side  $\approx 45 \dots 90^\circ$

Detection field  $\varnothing$ , on floor 0 m

**Materials**

Colour of design line polar white

Colour polarwhite

Material thermoplastic

**Lighting control**

Response brightness, adjustable  $\approx 5 \dots 1000$  lx , daytime operation

**Settings**

Response value luminosity adjustable Yes

Response value sensitivity adjustable Yes

Response sensitivity, settable 10...100 %

Delay time  $\approx 180$  s

Switch-off pre-warning to dimming value 50% for 30 s

**Safety**

Protection index IP IP20

Protection

with dismantling protection

---

**Use conditions**

---

Operating temperature

-5...45 °C

---

Relative humidity (without condensation)

0...65 % (without condensation)

---

**Identification**

---

Application, usage

Light control, Motion detector

---

Main design line

Berker Q.1/Q.3/Q.7/Q.9

---

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

---

**Instructions**

---

Information text

Continuous direct sunlight penetrating the upward--  
pointing detection plane can result in failure of the  
motion detector. Only suitable for indoor areas!