




80143329



Push-button 3gang, + RGB LED, internal temp. sensor, KNX - Q.1/Q.3, p. white

Technical properties

Functions

With room temperature controller Yes

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; Orientation LED can be controlled via object ; brightness value of the status LED for day/nighttime operation preset, status LED for day/nighttime operation can be controlled via object ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, temperature setpoint adjustment, operating mode changeover

Easy link functions

Function Function for manual interruption of automatic functions already triggered

operating surfaces as buttons (single-surface operation) and rockers (two-surface operation) ; the brightness of status LEDs are individually adjustable for button/ rocker function ; brightness value of the status LEDs for day/nighttime operation adjustable via object or manually ; value transmitter for dimming, position, brightness temperature values 1 and 2 byte ; button/rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, automatic control deactivation ; integrated temperature sensor with output of the measured values via object ; button functions for switching, dimming, roller shutter/blind, timer, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, 2-channel mode, step switch, automatic control deactivation ; rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, 2-channel mode, automatic control deactivation ; parameter defineable lock function ; 3-step switch, function for incremental selection of up to 7 stored values ; Status LED configurable in its colour per button

Function

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 3

Operation 1 or 2-push-button operation concept selectable

Electric current

Bus current consumption (data transfer) max. 20 mA

Dimensions

Labelling field length (W x H) 56.4 x 17 mm

Height	58.7 mm
Width	58.7 mm
Power	
Power consumption, KNX	≈ 150 mW
Measurement	
Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
Screen	
With display	No
Materials	
Colour of design line	polar white
Colour independent of design lines	polar white
RAL colour	RAL 9010 - Pure white
Material / workmanship	lacquered
Surface appearance	velvety
Surface protection	Varnished
Material family	Plastic
LED control	
LED	with white operating LED ; with 2 RGB status LEDs per rocker
Connection	
Bus coupling unit	for bus coupling unit flush-mounted
Settings	
Supported configuration modes	system, easy
Scope of delivery	
Bus connection included	No
Equipment	
Number of actuation points	6
With anti-theft/dismantling protection	Yes
Product type:	product type: push-button 3gang
Use	
Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 2 - Sales	and RGB LED
Differentiation characteristic 3 - Sales	with integrated temperature sensor
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

Temperature	integrated temperature sensor with output of the measured values via object
-------------	---

Identification

Application, usage	KNX - operating systems
--------------------	-------------------------

Product family	product family: push-button
----------------	-----------------------------

Main design line	KNX - Berker Q.1/Q.3
------------------	----------------------

Secondary design line(s)	KNX ; Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
--------------------------	---

Instructions

Special note text	Use only in conjunction with bus coupling unit 8004 00 01!
-------------------	--