



85341173

Motion det. 1.1 m, K.5, stainless steel matt, lacq.

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Function with keylock

Controls and indicators

Button / push-button with button for on/off/automatic

Dimensions

Assembling height 34 mm

Nominal mounting height 1.1 m

Measurement

Detection field, rectangular shaped $\approx 12 \times 16$ m

Reach distance

Range, frontal ≈ 12 m

Detection

Number of detection levels 3

Detection angle, settable each side $\approx 45 \dots 90^\circ$

Detection field \varnothing , on floor 0 m

Materials

Colour of design line stainless steel

Colour stainless steel

Material / workmanship lacquered

Material thermoplastic

Lighting control

Response brightness, adjustable $\approx 5 \dots 1000$ lx , daytime operation

Settings

Response value luminosity adjustable Yes

Response value sensitivity adjustable Yes

Response sensitivity, settable 10...100 %

Delay time ≈ 180 s

Switch-off pre-warning to dimming value 50% for 30 s

Safety

Protection index IP

IP20

Protection

with dismantling protection

Use conditions

Operating temperature

-5...45 °C

Relative humidity (without condensation)

0...65 % (without condensation)

Identification

Application, usage

Light control, Motion detector

Main design line

Berker K.5

Secondary design line(s)

Motion detector, Berker K.5

Instructions

Information text

Continuous direct sunlight penetrating the upward-pointing detection plane can result in failure of the motion detector. Only suitable for indoor areas!