



85341282

IR motion detector comfort 1.1 m, S.1, white glossy

Technical properties

Functions

Mode of operation μ-processor controlled mode of operation

Function Teach function for response brightness via button ;
with keylock ; Party function for switching on for 2
hours ; with memory function for presence simulation

Operating mode step operation with immunity time (e.g. for stair
light/impact current circuits)

Controls and indicators

Button / push-button with button for on/off/automatic

Dimensions

Assembling height 34 mm

Nominal mounting height 1.1 m

Tripping

immunity time ≈ 10 s

Measurement

Detection field, rectangular shaped ≈ 12 x 16 m

Reach distance

Range, frontal ≈ 12 m

Range, side each ≈ 8 m

Detection

Number of detection levels 3

Detection angle, settable each side ≈ 45...90 °

Detection field Ø, on floor 0 m

Materials

Colour of design line white

Colour white

Lighting control

Response brightness, adjustable ≈ 5...1000 lx , daytime operation

LED control

LED with operation and status LED, red/green/orange ;
LED application module/insert compatibility display

Settings

Response value luminosity adjustable Yes

Response value sensitivity adjustable	Yes
Response sensitivity, settable	10...100 %
Short time mode	200 ms
Delay time	≈ 180 s
Delay time, adjustable	≈ 10 s...30 mn
Switch-off pre-warning to dimming value 50% for	30 s

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Light control ; Motion detector
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Motion detector ; Berker S.1 ; Berker B.3 ; Berker B.7

Instructions

Information text	Continuous direct sunlight penetrating the upward-pointing detection plane can result in failure of the motion detector. Only suitable for indoor areas!
------------------	--