



85342185

Motion det. 2.2 m, S.1/B.3/B.7, ant., matt

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Function with keylock

Controls and indicators

Button / push-button with button for on/off/automatic

Dimensions

Assembling height 34 mm

Nominal mounting height 2.2 m

Measurement

Detection field, rectangular shaped $\approx 8 \times 12$ m

Reach distance

Range, frontal ≈ 8 m

Range, side each ≈ 6 m

Detection

Number of detection levels 3

Detection angle, settable each side $\approx 45 \dots 90^\circ$

Detection field \varnothing , on floor 0 m

Materials

Colour of design line anthracite

Colour anthracite

Material thermoplastic

Lighting control

Response brightness, adjustable $\approx 5 \dots 1000$ lx , daytime operation

Settings

Response value luminosity adjustable Yes

Response value sensitivity adjustable Yes

Response sensitivity, settable 10...100 %

Delay time ≈ 180 s

Switch-off pre-warning to dimming value 50% for 30 s

Safety

Protection index IP	IP20
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)
Identification	
Application, usage	Light control, Motion detector
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Motion detector, Berker S.1, Berker B.3, Berker B.7