



BA7A60080

## Slotted panel trunking made of PVC BA7A 60x80mm grey

### Technical properties

#### Architecture

|          |    |
|----------|----|
| Flexible | No |
|----------|----|

#### Configuration

|                         |         |
|-------------------------|---------|
| Side wall configuration | Slotted |
|-------------------------|---------|

#### Electric current

|                     |     |
|---------------------|-----|
| Current leak stable | Yes |
|---------------------|-----|

#### Dimensions

|                 |       |
|-----------------|-------|
| Trunking height | 60 mm |
|-----------------|-------|

|        |         |
|--------|---------|
| Length | 2000 mm |
|--------|---------|

|                |       |
|----------------|-------|
| Trunking width | 80 mm |
|----------------|-------|

|            |      |
|------------|------|
| Slot width | 6 mm |
|------------|------|

|              |        |
|--------------|--------|
| Tongue width | 6.5 mm |
|--------------|--------|

#### Cover, door

|           |       |
|-----------|-------|
| Lid shape | loose |
|-----------|-------|

#### Materials

|                |         |
|----------------|---------|
| Material group | plastic |
|----------------|---------|

|                           |           |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

#### Installation, mounting

|               |                   |
|---------------|-------------------|
| Base punching | EN 50085-2-3:1999 |
|---------------|-------------------|

|             |                 |
|-------------|-----------------|
| Fixing type | bottom punching |
|-------------|-----------------|

#### Cable

|  |     |
|--|-----|
| Number of wires 1,5 mm <sup>2</sup> - 40% filling degree | 139 |
|--|-----|

|                               |                      |
|-------------------------------|----------------------|
| Internal/useful cross section | 3658 mm <sup>2</sup> |
|-------------------------------|----------------------|

|  |    |
|--|----|
| Number of wires 2,5 mm <sup>2</sup> - 40% filling degree | 99 |
|--|----|

|  |     |
|--|-----|
| Number of wires 1,0 mm <sup>2</sup> - 40% filling degree | 193 |
|--|-----|

#### Standards

|           |             |
|-----------|-------------|
| Approvals | EN50085-2-3 |
|-----------|-------------|

|                         |                      |
|-------------------------|----------------------|
| European directive RoHs | voluntary compliance |
|-------------------------|----------------------|

|                      |    |
|----------------------|----|
| UL 94 classification | V0 |
|----------------------|----|

#### Safety

|                          |            |
|--------------------------|------------|
| REACH conform            | Yes        |
| RoHS conform             | Yes        |
| Halogen free             | No         |
| Fireproof classification | M1         |
| <b>temperatur</b>        |            |
| Ambient temperature      | -5...60 °C |