



85241183

Shutter push-button, S.1/B.7, al., matt, lacq.

Technical properties

Functions

Venetian blind movement time	2 mn
Function	Memory function for automatic execution of learned up and down times with position ; Party function, no execution of automatic, radio and extension unit commands (lock-out protection)

Controls and indicators

Operation	activation of the party function using buttons in up and down direction > 20 sec.
-----------	---

Main electrical features

Nominal voltage	12 V
Frequency	- Hz

Detection

Sensor	Not suitable for rain and wind sensors
--------	--

Materials

Colour of design line	aluminium
Colour	aluminium
Material / workmanship	lacquered
Material	thermoplastic

LED control

LED	LED application module/insert compatibility display ; with status LED for memory and party function, red/orange ; with indicator LED for lock-out protection
-----	--

Installation, mounting

Installation mode	clamp fastening
-------------------	-----------------

Settings

Lamella adjusting time	(adjustable) 50 ms...2.5 s
Minimum slat adjustment time	≈ 250 ms
Delay time, adjustable	0...500 s
Lamella adjustment on button-press	< 0.4 s

Equipment

Self-retaining for 2 min on button-press	> 0.4 s
Change-over time for change of direction	< 0.6 s

Safety

Protection

with dismantling protection

Use conditions

Operating temperature

-5...45 °C

Energy-saving

low intrinsic energy requirement

Relative humidity (without condensation)

0...65 % (without condensation)

Identification

Application, usage

Blind control

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Electronics platform ; Berker S.1 ; Berker B.3 ;
Berker B.7

Instructions

Special note text

Can be switched to orientation led by extension unit.