



85241185

**Shutter push-button, S.1/B.3/B.7, ant., matt**

**Technical properties**

**Functions**

Venetian blind movement time	2 mn
Function	Memory function for automatic execution of learned up and down times with position ; Party function, no execution of automatic, radio and extension unit commands (lock-out protection)

**Controls and indicators**

Operation	activation of the party function using buttons in up and down direction > 20 sec.
-----------	---

**Main electrical features**

Nominal voltage	12 V
Frequency	- Hz

**Detection**

Sensor	Not suitable for rain and wind sensors
--------	--

**Materials**

Colour of design line	anthracite
-----------------------	------------

**LED control**

LED	LED application module/insert compatibility display ; with status LED for memory and party function, red/orange ; with indicator LED for lock-out protection
-----	--

**Installation, mounting**

Installation mode	clamp fastening
-------------------	-----------------

**Settings**

Lamella adjusting time	(adjustable) 50 ms...2.5 s
Minimum slat adjustment time	≈ 250 ms
Delay time, adjustable	0...500 s
Lamella adjustment on button-press	< 0.4 s

**Equipment**

Self-retaining for 2 min on button-press	> 0.4 s
Change-over time for change of direction	< 0.6 s

**Safety**

Halogen free	No
Protection	with dismantling protection

**Use conditions**

Subject to technical modifications

---

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

---

**Identification**

---

Application, usage	Blind control
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Electronics platform ; Berker S.1 ; Berker B.3 ; Berker B.7

---

**Instructions**

---

Special note text	Can be switched to orientation led by extension unit.
-------------------	---

---