



85342124

Motion detector 2.2 m Q.x alu velvety lacquered

Technical properties

Architecture

Fixing mode flush-mounting

Functions

Function with keylock

Controls and indicators

Button / push-button with button for on/off/automatic

Dimensions

Assembling height 34 mm

Nominal mounting height 2.2 m

Measurement

Detection field, rectangular shaped $\approx 8 \times 12$ m

Reach distance

Range, frontal ≈ 8 m

Range, side each ≈ 6 m

Detection

Number of detection levels 3

Detection angle, settable each side $\approx 45 \dots 90^\circ$

Detection field \varnothing , on floor 0 m

Materials

Colour aluminium

Material / workmanship lacquered

Material thermoplastic

Lighting control

Response brightness, adjustable $\approx 5 \dots 1000$ lx , daytime operation

Settings

Response value luminosity adjustable Yes

Response value sensitivity adjustable Yes

Response sensitivity, settable 10...100 %

Delay time ≈ 180 s

Switch-off pre-warning to dimming value
50% for 30 s

Safety

Protection index IP

IP20

Protection

with dismantling protection

Use conditions

Operating temperature

-5...45 °C

Relative humidity (without condensation)

0...65 % (without condensation)

Identification

Application, usage

Light control, Motion detector

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9