



85342173

**Motion det. 2.2 m, K.5, stainless steel matt, lacq.**

#### Technical properties

##### Architecture

Fixing mode	flush-mounting
-------------	----------------

##### Functions

Function	with keylock
----------	--------------

##### Controls and indicators

Button / push-button	with button for on/off/automatic
----------------------	----------------------------------

##### Dimensions

Assembling height	34 mm
Nominal mounting height	2.2 m

##### Measurement

Detection field, rectangular shaped	≈ 8 x 12 m
-------------------------------------	------------

##### Reach distance

Range, frontal	≈ 8 m
Range, side	each ≈ 6 m

##### Detection

Number of detection levels	3
Detection angle, settable	each side ≈ 45...90 °
Detection field Ø, on floor	0 m

##### Materials

Colour of design line	stainless steel
Colour	stainless steel
Material / workmanship	lacquered
Material	thermoplastic

##### Lighting control

Response brightness, adjustable	≈ 5...1000 lx , daytime operation
---------------------------------	-----------------------------------

##### Settings

Response value luminosity adjustable	Yes
Response value sensitivity adjustable	Yes
Response sensitivity, settable	10...100 %
Delay time	≈ 180 s
Switch-off pre-warning to dimming value 50% for	30 s

<b>Safety</b>	
Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)
<b>Identification</b>	
Application, usage	Light control, Motion detector
Main design line	Berker K.5
Secondary design line(s)	Motion detector, Berker K.5